FABORY



Binnenzeskant passchroef UNC ASME B18.3 Staal Blank 012.9 (5/16)3/8X3/4

Artikelnummer	07116.079.019
Merk	-
UBB	953351304647
UNSPSC	31161605
EAN	8715492066619
PKG. van 10	Alleen volledige verpakkingen

Technische parameters

Lengte	3/4 Inch
Klasse	012.9
Aandraaivoorziening	Binnenzeskant
Kopsoort	Cilinderkop
Materiaalsoort	Staal
Draadrichting	Rechts
Oppervlaktebedekking	Blank
Draadsoort	Unified National Coarse
Info	Waarschuwing: bij het elektrolytisch behandelen van deze producten bestaat er gevaar voor het optreden van waterstofbrosheid.All dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread

Standaarden

ASME	B18.3
BS	2470

	tolerance class for these screws is 3A, plating can cause thread fit problems.

Technische specificatie

A (max.)	0.562
D	0.375
D1	0.3125
E	0.5
H (max.)	0.25
J	0.1875
Gangen per Inch	18
D (min.)	0.371
D (max.)	0.373

Technische tekening

