
FABORY



Set de asamblări **structurale -** șurub **hexagonal** parțial **filetat & piuliță** hexagonală **EN 15048** Oțel **Zincat 8.8/8 M16X300**

Cod Articol	01222.160.300
Marcă	-
UBB	500613346401
UNSPSC	31161620
EAN	8715494441582
PKG. of 25	Exclusiv împachetare

Parametri tehnici

Diameter	M16
Lungime	300 mm
Clasă	8.8/8
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel
Direcție filet	Dreapta
Tratament suprafaţă	Zincat
Filete	Filet metric
Info	Full boxes only.European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects.Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

Standarde

ISO	4014/4032
EN	15048

bolting according to EN 15048-1 are compliant with the CPR.Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark.The manufacturer of the assemblies is CE certified for their production.Bolts and nuts are packaged together in single sealed boxes.A Declaration of Performance (DoP) is available.

Specificatii tehnice

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	300
m (max.)	14.8
P	2
s	24

Desen tehnic

