
FABORY



Structural assembly set ISO metric thread EN 15048 Oțel Zincat termic 8.8/8 M16X80

Cod Articol	01405.160.080
Marcă	-
UBB	500574459961
UNSPSC	31161620
EAN	8715494283878
PKG. of 25	Exclusiv împachetare

Parametri tehnici

Diameter	M16
Lungime	80 mm
Clasă	8.8/8
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel
Direcție filet	Dreapta
Tratament suprafaţă	Zincat termic
Filete	Filet metric
Info	Full boxes only.European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects.Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural bolting according

Standarde

EN	15048
ISO	4014/4032

to EN 15048-1 are compliant with the CPR.Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark.The manufacturer of the assemblies is CE certified for their production.Bolts and nuts are packaged together in single sealed boxes.A Declaration of Performance (DoP) is available.ISO metric

Specificatii tehnice

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	80
m (max.)	14.8
P	2
s	24

Desen tehnic

