FABORY

Șurub **cu cap hexagonal complet filetat ISO 4017** Oțel **(AD-W7) Zincat 5.6 pentru vase de presiune M8X12**

Cod Articol	08761.080.012
Marcă	-
UBB	500648347457
UNSPSC	31161620
EAN	8717077244665
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diameter	M8
Lungime	12 mm
Clasă	5.6
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel (AD-W7)
Direcție filet	Dreapta
Tratament suprafaţă	Zincat
Filete	Filet metric
Info	Specific features of fasteners for pressure vessels:Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C.Meets the requirements of AD2000-W7, TRD106 and DIN 267-13.Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standarde

DIN	933
ASME	B18.2.3.1M
NF	E25-114
NEN	1568
ISO	4017

certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer’s mark. This recognition is equally accepted by Lloyd's Register Energy.for pressure vessels

Specificatii tehnice

d-D	M8
k	5.3
L (mm)	12
P	1.25
s	13

Desen tehnic

