
FABORY



12X120

Cod Articol	45795FIS
Marcă	-
UBB	500616730882
UNSPSC	31162101
EAN	4006209457955
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Caracteristici cheie	Functioning - The FWA is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS setting tool.
Info	do = Nominal diameter of drill bit.tfix = Grip range.hef = Effective anchorage

Standarde

depth.Min. td = Recommended drilling depth.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor γf= 1,4 and if the Scr, N and Ccr, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Specificatii tehnice

Desen tehnic

