FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M3X30

Article number	01000.030.030
Brand	-
UBB	500644571175
UNSPSC	31161620
EAN	8717077046740
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112
NEN	1555

Technical Specification

b (min.): L≤125mm	12
d-D	M3
k	2
L (mm)	30
P	0.5
s	5.5

Technical Drawing

