FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M3X40

Article number	01000.030.040
Brand	-
UBB	500644971136
UNSPSC	31161620
EAN	8717077046764
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): L≤125mm	12
d-D	M3
k	2
L (mm)	40
P	0.5
s	5.5

Technical Drawing

