FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X70

Article number	01000.100.070
Brand	-
UBB	950351005935
UNSPSC	31161620
EAN	8715492007674
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	70
P	1.5
s	17

Technical Drawing

