FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X85

Article number	01000.120.085
Brand	-
UBB	952351313723
UNSPSC	31161620
EAN	8715492008022
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	85 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	85
P	1.75
s	19

Technical Drawing

