FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M14X65

Article number	01000.140.065
Brand	-
UBB	950351009994
UNSPSC	31161620
EAN	8715492008275
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M14
Length	65 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	65
P	2
s	22

Technical Drawing

