FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M14X70

Article number	01000.140.070
Brand	-
UBB	950351903881
UNSPSC	31161620
EAN	8715492008282
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M14
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	70
P	2
s	22

Technical Drawing

