FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X130

Article number	01000.160.130
Brand	-
UBB	950351012378
UNSPSC	31161620
EAN	8715492008619
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	130
P	2
s	24

Technical Drawing

