FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X260

Article number	01000.160.260
Brand	-
UBB	950351013103
UNSPSC	31161620
EAN	8715492008749
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	260 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	260
P	2
s	24

Technical Drawing

