FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X100

Article number	01000.200.100
Brand	-
UBB	950351015918
UNSPSC	31161620
EAN	8715492009227
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	100
P	2.5
s	30

Technical Drawing

