FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X75

Article number	01000.240.075
Brand	-
UBB	950351019639
UNSPSC	31161620
EAN	8715492009791
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	75
P	3
s	36

Technical Drawing

