FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X400

Article number	01000.240.400
Brand	-
UBB	950351021775
UNSPSC	31161620
EAN	8715492010100
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	400 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	400
P	3
s	36

Technical Drawing

