FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X520

Article number	01000.300.520
Brand	-
UBB	500644583394
UNSPSC	31161620
EAN	8717077006881
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	520 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
DIN	931
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	520
P	3.5
s	46

Technical Drawing

