FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M42X190

Article number	01000.420.190
Brand	-
UBB	500644584954
UNSPSC	31161620
EAN	8717077007048
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M42
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	96
b (min.): L200mm	109
b (min.): L≤125mm	90
d-D	M42
k	26
L (mm)	190
P	4.5
s	65

Technical Drawing

