
FABORY



Flat countersunk square neck bolt with short square DIN ≈608 Steel Plain 8.8 M16X55

Article number	01036.160.055
Brand	-
UBB	500644988064
UNSPSC	31161612
EAN	8717077048454
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	55 mm
Class	8.8
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	≈608

Technical Specification

b (min.)	38
d-D	M16
dk (max.)	32
L (mm)	55
P	2
fn (max.)	13.5
v (max.)	16.7

Technical Drawing

