FABORY



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M18X240

Article number	01200.180.240
Brand	-
UBB	500644629270
UNSPSC	31161620
EAN	8717077011816
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M18
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	240
P	2.5
s	27

Technical Drawing

