FABORY



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M20X270

Article number	01200.200.270
Brand	-
UBB	500644629767
UNSPSC	31161620
EAN	8717077011861
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	270 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	270
P	2.5
s	30

Technical Drawing

