FABORY

Hexagon head screw DIN 933 Steel Zinc plated yellow passivated 8.8 M12X60/S=19

Article number	01230.120.060
Brand	-
UBB	950351179102
UNSPSC	31161620
EAN	8715492037046
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1568
NF	E25-114
ASME	B18.2.3.1M
ISO	4017
DIN	933

Technical Specification

d-D	M12
k	7.5
L (mm)	60
P	1.75
s	19

Technical Drawing

