FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M10X50/S=17

Article number	01400.100.050
Brand	-
UBB	950351188509
UNSPSC	31161620
EAN	8715492408228
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45

Technical Drawing

b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	50
P	1.5
s	17

