FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M22X75/S=34

Article number	01400.220.076
Brand	-
UBB	952351082971
UNSPSC	31161620
EAN	8715492409201
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M22
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	56
b (min.): L200mm	69

Technical Drawing

b (min.): L≤125mm	50
d-D	M22
k	14
L (mm)	75
P	2.5
s	34

FABORY

