FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M24X280

Article number	01400.240.280
Brand	-
UBB	950351940750
UNSPSC	31161620
EAN	8715492409522
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	280 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

ISO	4014
DIN	931
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73

Technical Drawing

b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	280
P	3
s	36

FABORY

