FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M20X80

Article number	04101.200.080
Brand	-
UBB	500648306446
UNSPSC	31161620
EAN	8717077207530
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NEN	1555
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	80
P	2.5
s	30

Technical Drawing

