FABORY

Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 10.9 M14X80/ S=22

Article number	04104.140.080
Brand	-
UBB	953351909890
UNSPSC	31161620
EAN	8715493175655
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M14
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
NF	E25-112
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	80

Technical Drawing

