FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M24X120

Article number	04105.240.120
Brand	-
UBB	500505565670
UNSPSC	31161620
EAN	8715494440608
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	120
P	3

Technical Drawing

