FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M10X100

Article number	04108.100.100
Brand	-
UBB	955351408757
UNSPSC	31161620
EAN	8715493849679
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	100 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	4014
NEN	1555
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	100
P	1.5
s	17

Technical Drawing

