FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M14X50

Article number	04108.140.050
Brand	-
UBB	955351409821
UNSPSC	31161620
EAN	8715493849785
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M14
Length	50 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
DIN	931
NEN	1555
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	50
P	2
s	22

Technical Drawing

