FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X85

Article number	07060.300.085
Brand	-
UBB	500644802679
UNSPSC	31161605
EAN	8717077028814
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	85 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1241
BS	4168-1
ASME	B18.3.1M
DIN	912
ISO	4762
NF	E25-125

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if L ≤	100
k (max.)	30
L (mm)	85
P	3.5
s	22

Technical Drawing

