FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X210

Article number	07060.300.210
Brand	-
UBB	500644802836
UNSPSC	31161605
EAN	8717077028838
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	210 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

BS	4168-1
NF	E25-125
DIN	912
ISO	4762
ASME	B18.3.1M
NEN	1241

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if L ≤	100
k (max.)	30
L (mm)	210
P	3.5
s	22

Technical Drawing

