FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M33X65

Article number	07060.330.065
Brand	-
UBB	500644805722
UNSPSC	31161605
EAN	8717077029125
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M33
Length	65 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.3.1M
BS	4168-1
NF	E25-125
ISO	4762
DIN	912
NEN	1241

Technical Specification

b	78
d-D	M33
dk (max.)	50
Full thread if L ≤	100
k (max.)	33
L (mm)	65
P	3.5
s	24

Technical Drawing

