
FABORY



Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M3X20

Article number	07150.030.020
Brand	-
UBB	950351944893
UNSPSC	31161518
EAN	8715492068538
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

BS	≈4168-6
ASME	≈B18.3.4M
ISO	7380-1
NF	≈E25-126

the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

d-D	M3
dk (max.)	5.7
Full thread if L ≤	20
k (max.)	1.65
L (mm)	20
P	0.5
s	2

Technical Drawing

