FABORY



Studbolt with 2 heavy hexagon nuts metric BS ≈4882 Steel ASTM A193M - ASTM A194M Plain Gr.B7 - Gr.2H M33X230

Article number	22060.330.230
Brand	-
UBB	500578859513
UNSPSC	31161619
EAN	8715494409612
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M33
Length	230 mm
Class	Gr.B7 - Gr.2H
Driving features	Hexagon
Material	Steel
Material technical	ASTM A193M - ASTM A194M
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Depending on availability studbolts may be supplied with nuts with WAF according to DIN 934 instead of ASME B18.2.4.6M.L is the nominal length of the studbolt not including the chamfered ends.

Standards

BS	≈4882
ASTM	A193/A194

Technical Specification

B	50
d-D	M33

Technical Drawing

L (mm)	230
M	33
P	3.5

