FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 1/2X65 (2.1/2)

Article number	22080.127.063
Brand	-
UBB	950353061829
UNSPSC	31161619
EAN	8715492616913
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1/2 Inch
Length	65 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Technical Specification

B	0.875

Technical Drawing

L (mm)	65
M	12.3

