FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 7/8X245 (9.5/8)

Article number	22080.222.245
Brand	-
UBB	500578024282
UNSPSC	31161619
EAN	8715494343435
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	245 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	9
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

Technical Specification

B	1.4375

Technical Drawing

L (mm)	245
M	21.8

