FABORY



# Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 7/8X405 (16)

| | |
|---|---|
| Article number | 22080.222.406 |
| Brand | - |
| UBB | 500578026832 |
| UNSPSC | 31161619 |
| EAN | 8715494343695 |
| PKG. of 1 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | 7/8 Inch |
| Length | 405 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Unified National Coarse |
| Threads per inch | 9 |
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |

## Standards

| | |
|---|---|
| ASTM | A193/A194 |
| ASME | B16.5/B18.2.2 |
| BS | ≈4882 |

## Technical Specification

| | |
|---|---|
| B | 1.4375 |

## Technical Drawing

| | |
|---|---|
| L (mm) | 405 |
| M | 21.8 |

