FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.7 1.1/2X205 (8.1/8)

Article number	22326.381.205
Brand	-
UBB	500578295957
UNSPSC	31161619
EAN	8715494339476
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/2 Inch
Length	205 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	2.375
L (mm)	205

Technical Drawing

M 37.3

FABORY

