FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X55

Article number	24520.080.055
Brand	-
UBB	500645194290
UNSPSC	31161504
EAN	8717077070059
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	55 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
DIN	84
NEN	≈1602

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	55
n	2
P	1.25
t (min.)	2

Technical Drawing