FABORY



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M3X14

Article number	24540.030.014
Brand	-
UBB	500645194522
UNSPSC	31161504
EAN	8717077070080
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	14 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
NF	≈E25-123
NEN	≈2370
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	14
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

