FABORY



# Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X22

| | |
|---|---|
| Article number | 24540.050.022 |
| Brand | - |
| UBB | 500645195511 |
| UNSPSC | 31161504 |
| EAN | 8717077070189 |
| PKG. of 1 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M5 |
| Length | 22 mm |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| DIN | 963 |
| BS | ≈4183 |
| NF | ≈E25-123 |
| ASME | ≈B18.6.7M |
| NEN | ≈2370 |
| ISO | ≈2009 |

## Technical Specification

| | |
|---|---|
| d-D | M5 |
| Thread length (min.) | 25 |
| dk (max.) | 9.2 |
| Full thread if L ≤ | 30 |
| k (max.) | 2.5 |
| L (mm) | 22 |
| n | 1.2 |
| P | 0.8 |
| t (min.) | 1 |

## Technical Drawing

