
FABORY



Slotted pan head screw DIN 85 Steel Plain 4.8 M5X35

Article number	24635.050.035
Brand	-
UBB	500649349908
UNSPSC	31161504
EAN	8717077265974
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	≈1603
ISO	≈1580
NF	≈E25-128
ASME	≈B18.6.7M
DIN	85
BS	≈4183

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3
L (mm)	35
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

