FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M8X12

Article number	51230.080.012
Brand	-
UBB	952351511722
UNSPSC	31161518
EAN	8715492276315
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	12 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ASME	B18.3.6M
ISO	4028
DIN	915
BS	4168-4
NEN	2344
NF	E27-182

Technical Specification

d-D	M8
dp (max.)	5.5
L (mm)	12
P	1.25
s	4
t (min.)	3
z long (min.)	4
z long if L ≥	12
z short (min.)	2

Technical Drawing

