FABORY



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M5X14

Article number	51300.050.014
Brand	-
UBB	500571536811
UNSPSC	31161504
EAN	8715494123204
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	14 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	14
No. cross recess	2
P	0.8

Technical Drawing

