FABORY



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M5X60

Article number	51302.050.060
Brand	-
UBB	951353122058
UNSPSC	31161504
EAN	8715492282439
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	60
No. cross recess	2
P	0.8

Technical Drawing

