FABORY



Retaining ring for bores - normal type DIN 472 Stainless spring steel 1.4122/1.4021 21MM

Article number	51437.021.001
Brand	-
UBB	950357356530
UNSPSC	31163202
EAN	8715492290151
PKG. of 1	Full Box Only

Technical Parameters

Diameter	21 mm
For nom. size	21mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size bore d1	21
Info	Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer.Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking.d4 is the minimum required installation space.During assembly it is essential to not over-compress the rings, a maximum compression of 0,99 x d1 is

Standards

DIN	472
BS	3673-4
NF	E22-165

recommended. For proper installation use pliers with spread limiter or assemble with the aid of a cone.

Technical Specification

Groove d2	22
Groove m (H13)	1.1
Groove n (min.)	1.5
Ring d3	22.5
Ring d4	12.2
Ring s	1
Ring b ≈	2.4

Technical Drawing

