FABORY



Retaining ring for bores - normal type DIN 472 Stainless spring steel 1.4122/1.4021 55MM

Article number	51437.055.001
Brand	-
UBB	950357149554
UNSPSC	31163202
EAN	8715492290403
PKG. of 1	Full Box Only

Technical Parameters

Diameter	55 mm
For nom. size	55mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size bore d1	55
Info	Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer.Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking.d4 is the minimum required installation space.During assembly it is essential to not over-compress the rings, a maximum compression of 0,99 x d1 is

Standards

DIN	472
NF	E22-165
BS	3673-4

recommended. For proper installation use pliers with spread limiter or assemble with the aid of a cone.

Technical Specification

Groove d2	58
Groove m (H13)	2.15
Groove n (min.)	4.5
Ring d3	59.2
Ring d4	40.7
Ring s	2
Ring b ≈	5

Technical Drawing

