FABORY



Bosch Stirring machine GRW12E-1200W

Article number	B4315.000.015
Brand	-
UBB	500624110820
UNSPSC	23101502
EAN	3165140754439
PKG. of 1	Full Box Only

Technical Parameters

Voltage	230
Nominal power consumption	1200
Machine weight	5.3
Max. torque	12
Tool insertion	M14
Max. on-load speed 1st gear	620
Idle rotational speed 1st gear	1000
Max. diameter of mixing garde	140

Standards