FABORY



Bosch Stirring machine GRW18 2 E-1800W

Article number	B4315.000.020
Brand	-
UBB	500624110903
UNSPSC	23101502
EAN	3165140754460
PKG. of 1	Full Box Only

Technical Parameters

Voltage	230
Nominal power consumption	1800
Machine weight	7.2
Max. torque	45
Tool insertion	M14
Max. on-load speed 1st gear	250
Max. on-load speed 2nd gear	580
Idle rotational speed 1st gear	450
Idle rotational speed 2nd gear	1050
Max. diameter of mixing garde	180

Standards